

Gas Flow Cell FCS16, 1/4" Fit, SC/PC



#72-176

Stock **#72-182** 1 In Stock

-

1

+

C\$1,575⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$1,575.00 each
Qty 5-9	C\$1,417.50 each
Need More?	Request Quote

Product Downloads

16.7	Path Length (cm):
>50%	Throughput (%):

SC/PC	Fiber Connector Type:
-------	-----------------------

General	
FCS	Type:
FCS-16-SS-1/4-SCPC	Model Number:

Optical Properties	
1260 - 1800	Wavelength Range (nm):

Environmental & Durability Factors	
0 to +70	Operating Temperature (°C):
-40 to +85	Storage Temperature (°C):

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Free Space and Fiber-Coupled Designs for UVthrough IR
- Stainless Steel Designs for Operation at High Temperatures and Pressures
- Designed for Easy Integration

Wavelength References Gas Flow Cells are designed for through-flow laser-based gas interrogation. The cells are housed in a rugged vacuum tight enclosure made of 316 stainless steel and feature Swagelok® tube fittings for gas inflow and outflow. We currently offer the following options:

- FCW (WIndowed Gas Flow Cells) are optimized for free space applications with a CaF2 window on the endcap, and feature a 10 cm path length and >50% transmission from 150nm to 9µm.
 - FCS (Single-Mode Fiber-Coupled Gas Flow Cells) are offered in both single mode and multimode configurations that correspond to 16.7 cm and 76.1 cm path lengths, respectively. Available with FC/PC, FC/APC, SC/PC, or SC/APC connectors, these flow cells feature SMF28e fiber for use in the 1260nm to 1800nm wavelength range, and can be operated from full vacuum to 1000 Torr.
 - FCM (Multimode Gas Flow Cells) are optimized for fiber optic and FTIR spectroscopy, and feature an SMA905 connectorized fiber, a 10 cm path length, and >50% transmission from 150nm to 9µm.
- Wavelength References Gas Flow Cells are ideal for gas sensing, chemical detection, and analytical spectroscopy applications.