

Fly's Eye Array 10 x 10mm, 300μm Pitch, 13° Divergence



Microlens Arrays



Stock **#83-910** ☐ In Stock

1

C\$987.00

ADD TO CART

Qty 1-10
C\$987.00
Qty 11+
C\$868.00
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
0.60

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:

Uncoated
Type: Fly's Eye Lens Array
Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±13
Lens Profile: Spherical
Pitch (µm): 300.00
Pitch Tolerance (µm): ±0.25
Radius R (mm): 0.293
Thickness (mm): 0.90
Thickness Tolerance (mm): ±0.05
Type of Optics: Double-Convex

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View