

SCHOTT GG-395, 25.4mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#46-055** ☐ In Stock

-

1

+

C\$54.25

ADD TO CART

Qty 1-10
C\$54.25
Qty 11+
C\$53.20
Volume Pricing
Request Quote

Get Product Downloads
Diameter (mm): 25.40
Cut-Off Position λ_c (nm): 395±6
Cut-On Wavelength (nm):

395.00
Density (g/cm³): 2.55
Glass/Filter Number: SCHOTT GG395
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 480.00
Passband Limit 2 λ_{p2} (nm): 700.00
Spectral Transmittance t_p (%): 92.00
Stopband Limit λ_s (nm): 340.00
Surface Quality: 80-50
Transformation Temperature (°C): 538.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View