


SCHOTT GG-395, 50.8mm Sq., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#46-056** ☐ In Stock

- 1 +

C\$123.20

ADD TO CART

Qty 1-10
C\$123.20
Qty 11+
C\$109.20
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 50.8 x 50.8
Cut-Off Position λ_c (nm): 395±6
Cut-On Wavelength (nm):

395.00
Density (g/cm³): 2.55
Glass/Filter Number: SCHOTT GG395
Length (mm): 50.80
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 480.00
Passband Limit 2 λ_{p2} (nm): 700.00
Spectral Transmittance t_p (%): 92.00
Stopband Limit λ_s (nm): 340.00
Surface Quality: 80-50
Transformation Temperature (°C): 538.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: UV
Width (mm): 50.80
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Compliant