

Coherent® Thermopile Power Sensor 1098498 | 100mW - 30W, UV Coating, DB25

See More by [Coherent®](#)



Stock **#12-406** [CONTACT US](#)

- 1 +

C\$2,135.00

ADD TO CART

Qty 1+
C\$2,135.00

Volume Pricing
Request Quote

Get Product Downloads

Active Area Diameter (mm):
19

Model Number:
PM30X
Coherent Part Number: 1098498

Resolution:
10mW

Type:

Meterless
Type of Sensor: Thermopile
Length of Cable (m): 2.0
Computer Interface: DB25
Calibration Uncertainty (%): ±1
Calibration Wavelength (nm): 514
Long Pulse Joule Mode Range (J): 0.5 - 50
Maximum Intermittent Power, <5min (W): 50 (air-cooled)
Cooling Method: Air
Maximum Incident Power Density (kW/cm²): 6
Power Range: 100mW - 30W
Maximum Incident Energy Density (J/cm²): 0.6 @ 1064nm, 10ns
Wavelength Range (nm): 150 - 1000
Wavelength Range (µm): 0.15 - 1

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View