

[See all 10 Products in Family](#)

Coherent® Thermopile Power Sensor 1098498 | 100mW - 30W, UV Coating, DB25

See More by [Coherent®](#)



Stock **#12-406** [CONTACT US](#)

-

1

+

C\$2,093^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,093.00 each
Need More?	Request Quote

Product Downloads

General	
Model Number:	
PM30X Coherent Part Number: 1098498	
Type:	
Meterless	
Calibration Uncertainty (%):	
±1	
Long Pulse Joule Mode Range (J):	

0.5 - 50	
Air	Cooling Method:
Maximum Incident Energy Density (J/cm²): 0.6 @ 1064nm, 10ns	
Physical & Mechanical Properties	
19	Active Area Diameter (mm):
Optical Properties	
10mW	Resolution:
514	Calibration Wavelength (nm):
150 - 1000	Wavelength Range (nm):
0.15 - 1	Wavelength Range (µm):
Sensor	
Thermopile	Type of Sensor:
Electrical	
50 (air-cooled)	Maximum Intermittent Power, <5min (W):
6	Maximum Incident Power Density (kW/cm²):
100mW - 30W	Power Range:
Hardware & Interface Connectivity	
2.0	Length of Cable (m):
DB25	Computer Interface:
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Superior Damage Resistance
- Wide Dynamic Range
- ISO 17025 Certified

Coherent® Thermopile Power Sensors are ideal for measuring the average power of continuous wave lasers or pulsed laser energy. Thermopile sensors operate by absorbing and converting incident laser radiation into heat, which then flows to a heat sink. The temperature difference between the absorber and heat sink is converted into an electrical signal by a thermocouple junction. Coherent® Thermopile Power Sensors, unlike semiconductor sensors, do not saturate. Unlike semiconductor sensors, thermopile sensors feature high power capability and flat spectral response.