

IDS Imaging Autofocusing USB 2.0 Compact Camera System

See More by [IDS Imaging Development Systems](#)



IDS Imaging Autofocusing USB 2.0 Compact Camera System

Stock **#14-125** CLEARANCE ☐ **In Stock**

-

1

+

C\$377.93

ADD TO CART

Qty 1+

C\$377.93

Volume Pricing

[Request Quote](#)

Get Product Downloads

Video Output:
USB 2.0

Type:
Color Camera

Manufacturer:
IDS Imaging

Mounting Threads:
No Mounting Threads/Tripod Adapter

Working Distance (mm):

100 - ∞
Image Buffer: 0MB
Note: Lens included
Camera Family: uEye XS
Model Number: UI-1007XS-C
Imaging Sensor: OmniVision OV5640
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Rolling
Camera Sensor Format: 1/4"
Resolution (MegaPixels): 5.00
Pixels (H x V): 2,592 x 1,944
Pixel Size, H x V (µm): 1.4 x 1.4
Sensing Area, H x V (mm): 3.63 x 2.72
Frame Rate (fps): 15.00
Pixel Depth: 8 bit
Exposure Time: 126µs - 1.17s
Connector: USB 2.0, Type Mini-B
Power Supply: Power over USB
Power Consumption (W): 1 - 1.1
GPIOs: N/A
Synchronization: Not Applicable
Dimensions (mm): 26.5 x 23.0 x 21.5 (includes lens and connectors)
Weight (g): 12
Housing: Full
Interface Port Orientation: Side Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): 0 to +55
Storage Temperature (°C): -20 to +60
GPIO Connector Type: None
Machine Vision Standard: IDS Software Suite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant