

Dual Bandpass VIS-NIR filter M37



Stock #74-536 NEW CONTACT US

⊖ 1 ⊕ C\$222.⁶⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$222.60 each
Need More?	Request Quote

Product Downloads

Full Width-Half Max FWHM Range (nm):
110nm, 375nm ±10 nm

General

Dual Bandpass Mounted Imaging Filter **Type:**

DB395/870-37 **Model Number:**

Physical & Mechanical Properties

39 **Outer Diameter (mm):**

Substrate Thickness (mm):

2mm

Optical Properties

AR **Coating:**

VIS-NIR **Color:**

40/20 **Surface Quality:**

≥90% **Transmission (%):**

Transmission Wavelength (nm):
375-425nm, 745-970nm

Threading & Mounting

M37 x 0.75 **Filter Thread:**

5.2 **Mount Thickness (mm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

Note: Other filter threads are available upon request.