

DUV Waveplate $\lambda/2$ 257nm 12.7mm Dia



Stock #29-969 **7 In Stock**

- 1 + C\$714.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | C\$714.00 each |
| Qty 6+ | C\$555.80 each |
| Need More? | Request Quote |

Product Downloads

General

Crystalline Waveplate **Type:**

Air spaced; no mounting glue; no glue contacted spacer between crystals **Configuration:**

Physical & Mechanical Properties

>7 **Clear Aperture CA (mm):**

Diameter (mm):

12.70 +0.00/-0.25

6.00 **Thickness (mm):**

Crystalline **Construction:**

<3 **Parallelism (arcsec):**

Optical Properties

Laser V-Coat (257nm) **Coating:**

257 **Design Wavelength DWL (nm):**

Crystal Quartz **Substrate:**

$\lambda/2$ **Retardance:**

10-5 **Surface Quality:**

$\lambda/10$ @632.8nm **Transmitted Wavefront, P-V:**

$\pm\lambda/100$ @20°C **Retardance Tolerance:**

0.0001 **Temperature Coefficient ($\lambda^\circ\text{C}$):**

R<0.2% @257nm **Coating Specification:**

0 **Retardance Order:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

Product Details

- 257nm and 266nm Deep UV Wavelengths Available
- Ideal For Vacuum Compatible Applications
- Non-Anodized Mount and Adhesive-Free Construction

DUV Vacuum-Compatible Waveplates are mounted in an unanodized aluminum housing and feature adhesive-free construction for low outgassing in vacuum environments. These waveplates are optimized for >99.8 transmission at 257 or 266nm designed wavelengths, with $\lambda/2$ or $\lambda/4$ retardance options for each. Featuring a superior retardation tolerance and zero-order construction, these waveplates have increased bandwidth and lower sensitivity to temperature change. DUV Vacuum-Compatible Waveplates have the fast axis marked on the edge of the mount for easy identification and system integration. These waveplates are ideal for life-science and lithography applications which require a vacuum environment.