

# IDS U3-3881LE-C-HQ-VU-AF, USB 3.0, 1/1.8" Color Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (C/CS - Mount, Full Housing, Front View)



Stock **#78-146** [CONTACT US](#)

-

1

+

C\$798<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$798.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

## SPECIFICATIONS

Color

Spectrum:

General

|                                                   |                             |
|---------------------------------------------------|-----------------------------|
| Color Camera                                      | Type:                       |
| U3-3881LE-C-HQ-WJ-AF                              | Model Number:               |
| IDS Imaging Development Systems                   | Manufacturer:               |
| uEye+ LE-AF                                       | Camera Series:              |
| Physical & Mechanical Properties                  |                             |
| 36 x 36 x 26 (excludes connectors and lens mount) | Dimensions (mm):            |
| 16                                                | Weight (g):                 |
| Board Level                                       | Housing:                    |
| Sensor                                            |                             |
| Not Specified                                     | Image Buffer:               |
| 1/1.8"                                            | Sensor Format:              |
| 6.40                                              | Resolution (Megapixels):    |
| 54.00                                             | Frame Rate (fps):           |
| 3,088 x 2,076                                     | Pixels (H x V):             |
| 2.40 x 2.40                                       | Pixel Size, H x V (µm):     |
| 7.411 x 4.982                                     | Sensing Area, H x V (mm):   |
| Sony IMX178                                       | Imaging Sensor:             |
| Progressive Scan CMOS                             | Type of Sensor:             |
| Rolling                                           | Shutter Type:               |
| 12 bit                                            | Pixel Depth:                |
| 0.014ms - 1090ms                                  | Exposure Time:              |
| 71.00                                             | Dynamic Range (dB):         |
| USB3 Vision                                       | Machine Vision Standard:    |
| Electrical                                        |                             |
| 1 - 1.5                                           | Power Consumption (W):      |
| Hardware & Interface Connectivity                 |                             |
| USB 3.0                                           | Interface:                  |
| USB Type-C                                        | Connector:                  |
| Power over USB                                    | Power Supply:               |
| 10-pin Wuerth connector (WR-WTB 1.00 mm)          | GPIO Connector Type:        |
| Threading & Mounting                              |                             |
| S-Mbunt (M12 x 0.5)                               | Mount:                      |
| Environmental & Durability Factors                |                             |
| 0 to +55                                          | Operating Temperature (°C): |
| -20 to +80                                        | Storage Temperature (°C):   |
| Regulatory Compliance                             |                             |
| View                                              | Certificate of Conformance: |

## PRODUCT DETAILS

- Up to 8.0MP Resolution with Framerrates up to 230fps
- Board Level Options with C/CS-Mount or S-Mount Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GenICam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mount or C/CS-Mount versions. The C/CS-Mount configurations come with a 5mm spacer to easily adapt between C-Mount and CS-Mount lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.

## CALIBRATION SERVICES

