

TECHSPEC® Elliptical Mirror 57.15mm Minor Axis Protected Gold



Stock **#32-090** ☐ In Stock

1 **C\$576.80**

ADD TO CART

Qty 1-5
C\$576.80
Qty 6+
C\$461.30
Volume Pricing
Request Quote

Get Product Downloads



Minor Axis (mm):
57.15

Major Axis (mm):
80.82

Surface Flatness (P-V):
λ/8

Substrate:

[BOROFLOAT®](#)

Surface Quality:
60-40

Dimensional Tolerance (mm):
±0.79

Dimensional Tolerance (inches):
±0.031

Coating Specification:
R_{avg} >96% @ 700 - 2000nm
R_{avg} >96% @ 2000 - 10,000nm

Coating:
Protected Gold (700-10000nm)

Coating Type:
Metal

Clear Aperture CA (mm):
51.44 (Minor Axis)
72.75 (Major Axis)

Note:
Flatness specification is Peak to Valley

Thickness (mm):
15.88

Thickness Tolerance (inches):
±0.060

Thickness Tolerance (mm):
±1.52

Type:
Flat Mirror

Wavelength Range (µm):
0.7 - 10

Wavelength Range (nm):
700 - 10000

Damage Threshold, Reference: ☐
0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)