

## Acetylene Fiber-Coupled Gas Cell, 3 cm Path Length, FC/APC



Stock #72-204 **1 In Stock**

⊖ 1 ⊕ C\$819<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	C\$819.00 each
Qty 5-9	C\$737.10 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

3 Path Length (cm):

FC/APC Fiber Connector Type:

### General

Acetylene (<sup>12</sup>C<sub>2</sub>H<sub>2</sub>) Type:

C2H2-12-H(3)-200-FCAPC Model Number:

### Optical Properties

---

1510 - 1540      **Wavelength Range (nm):**

>50      **Transmission (%):**

## Environmental & Durability Factors

+5 to +70      **Operating Temperature (°C):**

## Regulatory Compliance

[View](#)      **Certificate of Conformance:**

---

## Product Details

- Hydrogen Cyanide and Acetylene Gasses Available for Wavelength Coverage of 1510 to 1565nm
- FC and SC Fiber Connection Options with a Variety of Path Lengths Available
- NIST Traceable Reference Cells

Wavelength References Fiber-Coupled Gas Cells are FC/APC, SC/APC, FC/PC, or SC/PC connected fiber coupled, gas filled precision filters whose absorption wavelengths depend on specific molecular energy level transitions that may be used as wavelength standards. Hermetically sealed to maintain >10 year lifetime, these gas cells feature metal housings, wedged windows, and coated optics for minimum interference artifacts and can be easily integrated into existing benchtop systems. Wavelength References Fiber-Coupled Reference Cells are available with a variety of path lengths and pressures which meet the requirements of NIST Standard Reference Material® (SRMs) 2517a, 2519, or 2519a. Short path lengths are recommended for measuring gasses at high concentration while longer path lengths enable more sensitive measurements. These reference cells are ideal for spectroscopy, wavelength/frequency locking, laser calibration, and optical gas sensing systems. Hydrogen Cyanide ( $H^{13}C^{14}N$ ) has been identified by national standards bodies as the primary wavelength reference in the C-band (1530 – 1565nm) while Acetylene ( $^{12}C_2H_2$ ) is recognized as a primary wavelength reference in the 1510 to 1540nm band.