

Laminated Wratten ND Filter 0.1 OD 25mm Dia



Stock **#29-313** 20+ In Stock

-

1

+

C\$140^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	C\$140.00 each
Qty 11-25	C\$113.40 each
Need More?	Request Quote

Product Downloads

General	
Neutral Density Filter	Type:
Supplied with protective film on both sides	Note:
Physical & Mechanical Properties	
25.00 +/- 0.25	Diameter (mm):
Optical Properties	

0.1	Optical Density OD (Average):
Wratten 2 Filter, One-Side Laminated onto PMMA	Substrate:
Uncoated	Coating:
400-700	Blocking Wavelength Range (nm):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- One-Side Laminated for Stability
 - Available in 25mm and 48mm Sizes
 - Kodak Filter No. 96
 - Lightweight Alternative to Traditional Glass ND Filters
- PMMA-Laminated Wratten ND Filters are ideal for light attenuation in image-forming optical systems to reduce light intensity across the visible spectrum without altering the spectral profile. The laminated design offers additional stability and durability compared to traditional polyester/gelatin filters while remaining a lightweight alternative to traditional glass ND filters. These ND filters are available in 25mm or 48mm diameters and a thickness of 0.6mm. PMMA-Laminated Wratten ND Filters are uncoated and feature a blocking wavelength of 400 - 700nm with OD options of 0.1, 0.3, 0.5, 1.0, 2.0, and 3.0.