

[See all 12 Products in Family](#)

Laminated Wratten ND Filter 0.3 OD 25mm Dia



Stock #29-314 **20+ In Stock**

- 1 + C\$140⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	C\$140.00 each
Qty 11-25	C\$113.40 each
Need More?	Request Quote

Product Downloads

General

Neutral Density Filter **Type:**

Supplied with protective film on both sides **Note:**

Physical & Mechanical Properties

25.00 +/- 0.25 **Diameter (mm):**

Optical Properties

0.3 **Optical Density OD (Average):**

Substrate:
Wratten 2 Filter, One-Side Laminated onto PMMA

Coating:
Uncoated

Blocking Wavelength Range (nm):
400-700

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- One-Side Laminated for Stability
- Available in 25mm and 48mm Sizes
- Kodak Filter No. 96
- Lightweight Alternative to Traditional Glass ND Filters

PMMA-Laminated Wratten ND Filters are ideal for light attenuation in image-forming optical systems to reduce light intensity across the visible spectrum without altering the spectral profile. The laminated design offers additional stability and durability compared to traditional polyester/gelatin filters while remaining a lightweight alternative to traditional glass ND filters. These ND filters are available in 25mm or 48mm diameters and a thickness of 0.6mm. PMMA-Laminated Wratten ND Filters are uncoated and feature a blocking wavelength of 400 - 700nm with OD options of 0.1, 0.3, 0.5, 1.0, 2.0, and 3.0.