

[See all 12 Products in Family](#)

Laser Detection Wand IR



Laser Detection Products



Stock **#55-295** 20+ In Stock

-

1

+

C\$277²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$277.20 each
Qty 6-24	C\$263.20 each
Need More?	Request Quote

Product Downloads

General

Type:	Wand
Typical Applications:	808nm, 820nm, 830nm, 880nm, 960 - 980nm Laser Diodes, Nd:YAG, 1550nm Telecommunications

Physical & Mechanical Properties

Active Area Diameter (mm):	
----------------------------	--

17.00	
Disk: 25, Wand: 130 x35	Dimensions (mm):
Optical Properties	
IR	Wavelength:
Green (550nm), other peaks at Red (673nm) and Blue (400nm)	Emission Color:
Band 1: 790 - 840nm Band 2: 870 - 1070nm Band 3: 1500 - 1590nm	Stimulation Range:
250 kW/cm ² @ 1064nm, 7ns, 10Hz	Minimum Stimulation, Pulsed:
Electrical	
800 μs	Persistence (Stimulation Removed):
<2 μW/cm ² @ 808nm <175 nW/cm ² @ 960nm <100 μW/cm ² @ 1550nm	Minimum Stimulation, Continuous:
100 W/cm ² @ 1064nm	Maximum Stimulation, Continuous:
35 MW/cm ² @ 1064nm, 7ns	Maximum Stimulation, Single Pulse:
Regulatory Compliance	
Compliant	Reach 191:
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

• Full Spectrum Coverage: UV, VS, IR Series


• 3 Mounted Formats Have Safe, Non-reflective Encapsulation

• Unique, No Pre-charge for IR Detection and No Fading During Use

• Flexibility for Either Transmission or Reflective Viewing





Laser Detection Products offer UV, visible, and IR laser users' greater performance and safety. They reduce problems associated with beam visualization, profiling, and alignment in many applications. Each range is available in three formats. Laser Detection Products' laminated credit card style is for low-power sources and reflective viewing only. The 25mm disk and clip-on wand style is used when frequent component positioning is required. The removable disk is positional at an optics location to enable precise alignment, while the wand format permits handling into the beam path. The optical bench-mountable head format has a large active area and ¼-20 threaded mounting for standard English post/post holder integration.

Technical Information



IR Detection Products

Laser Detection Products				
	UV	VS	IR	NIR
Stimulation Range	250 - 550nm	Band 1: 400 - 640nm	Band 1: 790 - 840nm	700 - 1400nm
		Band 2: 800 - 1700nm	Band 2: 870 - 1070nm	
			Band 3: 1550nm	

Typical Applications	HeCd, Ar-Ion, tripled Nd:YAG, etc.	Ar-Ion, HeNe, HeCd, Nd:YAG, etc.	808nm, 820nm, 830nm, 880nm, 960 - 980nm Laser Diodes, Nd:YAG, 1550nm telecommunications	Nd:YAG, Fiber Laser
Emission Color	Yellow (580nm), Broadband (490nm - 700nm)	Orange/Red (655nm), Broadband (600 - 730nm)	Green (550nm), other peaks at Red (673nm) and Blue (400nm)	Orange/Red (655nm)
Persistence (Stimulation Removed)	6 s - 4 mins (dependent on ambient light)	Visible: 0.5 - 3 s (dependent on ambient light) IR: <0.5 s	800µs	<50 ms
Continuous (Minimum Stimulation)*	<1nW/cm ² @ 450nm & 365nm	<1nW/cm ² @ 450nm <25µW/cm ² @ 950nm	<2µW/cm ² @ 808nm <175 nW/cm ² @ 960nm <100µW/cm ² @ 1550nm	8µW/cm ² @ 1064nm
Pulsed (Minimum Stimulation)*	<8W/cm ² @ 337nm, 4ns, 20Hz, <40W/cm ² @ 337nm, 4ns, 1Hz	2 kW/cm ² @ 1064nm, 7ns, 10Hz	250 kW/cm ² @ 1064nm, 7ns, 10Hz	N/A
Continuous (Maximum Stimulation)	100W/cm ² @ 512nm (all formats)	100W/cm ² @ 512nm (all formats)	100W/cm ² (all formats)	100W/cm ² @ 1064nm (estimated)
Single Pulse (Maximum Stimulation)	130MW/cm ² @ 337nm, 4ns (card only) 850MW/cm ² @ 337nm, 4ns (other formats) 60MW/cm ² @ 1064nm, 7ns (all formats)	130MW/cm ² @ 337nm, 4ns (card only) 850MW/cm ² @ 337nm, 4ns (other formats) 60MW/cm ² @ 1064nm, 7ns (all formats)	35MW/cm ² @ 1064nm, 7ns (all formats)	35MW/cm ² @1064nm, 7ns (estimated)
				

*Measured in darkened conditions