

# Harsh Environment Transmission Dip Probe Tip, 5 mm

See More by [Ocean Optics](#)



Stock #90-584 NEW **1 In Stock**

⊖ 1 ⊕ C\$772<sup>00</sup>

**ADD TO CART**

#### Volume Pricing

Qty 1+	C\$772.80 each
Need More?	<a href="#">Request Quote</a>

#### Product Downloads

##### Construction Material:

Titanium

#### General

##### Model Number:

RT-TI-5MM

#### Optical Properties

##### Wavelength Range (nm):

200 - 2500

#### Regulatory Compliance

##### RoHS 2015:

[Compliant](#)

##### Certificate of Conformance:

[View](#)

##### Reach 250:

[Compliant](#)

## Product Details

- Transmission Dip Probes Designed for Reliable In-Solution Absorbance/Transmission Measurements
- Rugged Stainless Steel or PEEK for Tough Process Conditions and Harsh Environments
- Flexible Path Lengths Available with Interchangeable Probe Tips
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics Transmission Dip Probes couple to spectrometers and light sources to measure absorbance and transmission in solutions. Choose from ruggedized high-pressure probe ([#90-569](#)) for demanding process environments or PEEK-jacketed probes ([#90-570](#) and [#90-571](#)) for harsh chemical conditions, spanning UV-Vis to MS-NIR wavelengths. Easily customize your setup with accessories such as interchangeable probe tips in various path lengths and the protective sleeve ([#90-585](#)) for extended durability in corrosive or high-temperature applications. Ocean Optics Transmission Dip Probes are designed for seamless integration with [Ocean Optics spectroscopy systems and compatible accessories](#).

## Technical Information

Transmission Dip Probe	Transmission Dip Probe Stock Number	Compatible Transmission Dip Probe Tip	Compatible Transmission Dip Probe Tip Stock Number
UV-Vis Heavy-Duty Transmission Dip Probe	<a href="#">#90-569</a>	Harsh Environment Transmission Dip Probe Tip, 2 mm	<a href="#">#90-582</a>
		Harsh Environment Transmission Dip Probe Tip, 5 mm	<a href="#">#90-584</a>
		Harsh Environment Transmission Dip Probe Tip, 10 mm	<a href="#">#90-580</a>
		Harsh Environment Transmission Dip Probe Tip, 25 mm	<a href="#">#90-581</a>
		Harsh Environment Transmission Dip Probe Tip, 50 mm	<a href="#">#90-583</a>
UV-Vis Transmission Dip Probe	<a href="#">#90-570</a>	Stainless Steel Transmission Dip Probe Tip, 2 mm	<a href="#">#90-573</a>
		Stainless Steel Transmission Dip Probe Tip, 5 mm	<a href="#">#90-576</a>
		Stainless Steel Transmission Dip Probe Tip, 10 mm	<a href="#">#90-572</a>
		Adjustable Path Length Transmission Dip Probe Tip, 2–10 mm	<a href="#">#90-578</a>
		Adjustable Path Length Transmission Dip Probe Tip, 10–20 mm	<a href="#">#90-577</a>
MS-NIR Transmission Dip Probe	<a href="#">#90-571</a>	Stainless Steel Transmission Dip Probe Tip, 2 mm	<a href="#">#90-573</a>
		Stainless Steel Transmission Dip Probe Tip, 5 mm	<a href="#">#90-576</a>
		Stainless Steel Transmission Dip Probe Tip, 10 mm	<a href="#">#90-572</a>
		Adjustable Path Length Transmission Dip Probe Tip, 2–10 mm	<a href="#">#90-578</a>
		Adjustable Path Length Transmission Dip Probe Tip, 10–20 mm	<a href="#">#90-577</a>