

TECHSPEC®

PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 12.7mm Dia., 6.35mm Thick



Stock #29-520 **11 In Stock**

⊖ 1 ⊕ C\$434.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$434.00 each
Qty 6-25	C\$411.60 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

12.70 +0.00/-0.10	Diameter (mm):
6.35 ±0.10	Thickness (mm):
Commercial Polish	Edges:
	Bevel:

Protective as needed

Optical Properties

10-5 **Surface Quality:**

Coating Specification:
R_s > 99.50% @ 840 - 1010nm @ 45° AOI
R_p > 99.50% @ 870 - 980nm @ 45° AOI

GDD Specification:
0±50 fs² @ 840 - 1010nm @ 45° AOI (s-pol)
0±50 fs² @ 880 - 960nm @ 45° AOI (p-pol)

λ/10 **Surface Flatness (P-V):**

Design Wavelength DWL (nm):
840 - 1010, 870 - 980

Damage Threshold, Reference: □
0.5J/cm² @ 920nm, 100-on-1, S-Polarization, 5Hz,
Pulse Duration 25fs, 350μm Dia.

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- High Femtosecond Laser Damage Threshold exceeding 0.75J/cm² for 25fs Pulse Duration at 920nm
- > 99.5% Reflectivity with Near Zero Group Delay Dispersion
- [Platinum-Level 2024 Laser Focus World \(LFW\) Innovators Award](#)

TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors utilize an innovative design approach to maximize laser damage threshold for ultrafast pulses. These mirrors boast a near 0fs² GDD over a broad spectral bandwidth, making them suitable for the most demanding ultrafast applications. A 45° angle of incidence makes them perfectly suitable as turn mirrors in advanced ultrafast laser systems. TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors' high reflectivity ensures minimal loss while maintaining ultrashort pulse durations. The outstanding high laser damage threshold (LDT) values exceeding 0.75J/cm² for 25fs Pulse Duration at 920nm for these mirrors ensures they will perform even under exceptionally high ultrafast pulse energies.

Coating Curves