

[See all 6 Products in Family](#)

TECHSPEC®

Max PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 12.7mm Dia., 6.35mm Thick



Stock #29-523 **20+ In Stock**

⊖ 1 ⊕ C\$512⁰⁰

ADD TO CART

Volume Pricing

Qty 1-5	C\$512.40 each
Qty 6+	C\$488.60 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

12.70 +0.00/-0.10 **Diameter (mm):**

6.35 ±0.10 **Thickness (mm):**

Commercial Polish **Edges:**

Bevel:

Protective as needed

Optical Properties

10-5 **Surface Quality:**

Coating Specification:
R_s > 99.50% @ 830 - 1010nm @ 45° AOI
R_p > 99.50% @ 840 - 997nm @ 45° AOI

GDD Specification:
0 ± 50 fs² @ 830 - 1010nm @ 45° AOI (s-pol)
0 ± 50 fs² @ 861 - 966nm @ 45° AOI (p-pol)

λ/10 **Surface Flatness (P-V):**

830 - 1010 **Design Wavelength DWL (nm):**

Damage Threshold, Reference: □
0.75J/cm² @ 920nm, 100-on-1, S-Polarization, 5Hz,
Pulse Duration 25fs, 350μm Dia.

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- High Femtosecond Laser Damage Threshold exceeding 0.75J/cm² for 25fs Pulse Duration at 920nm
- > 99.5% Reflectivity with Near Zero Group Delay Dispersion
- [Platinum-Level 2024 Laser Focus World \(LFW\) Innovators Award](#)

TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors utilize an innovative design approach to maximize laser damage threshold for ultrafast pulses. These mirrors boast a near 0fs² GDD over a broad spectral bandwidth, making them suitable for the most demanding ultrafast applications. A 45° angle of incidence makes them perfectly suitable as turn mirrors in advanced ultrafast laser systems. TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors' high reflectivity ensures minimal loss while maintaining ultrashort pulse durations. The outstanding high laser damage threshold (LDT) values exceeding 0.75J/cm² for 25fs Pulse Duration at 920nm for these mirrors ensures they will perform even under exceptionally high ultrafast pulse energies.

Coating Curves