

LightPath 354220 | 1310nm Alignment, 0.25 NA Fiber Collimator w/ FC/APC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#16-708** CLEARANCE ☐ In Stock

1 **C\$247.73**

ADD TO CART

Qty 1+

C\$247.73

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):
11.00 @ 633nm

Numerical Aperture NA:
0.25

Substrate: ☐
[D-ZK3](#)

Coating:

BBAR (1050-1600nm)
Coating Specification: R _{abs} <1.0% @ 1050 - 1600nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.50
f/#: 2.00
Bevel: Protective bevel as needed
Connector: FC/APC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 22.73
Lightpath Lens Code: 354220
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 1050 - 1600
Conjugate Distance: Infinite
Alignment Wavelength (nm): 1310

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant