

Lightpath 7100350 | 15mm FL, f/1.0, Thermal Imaging Lens Assembly

See More by [Lightpath®](#)



Stock #15-689 CLEARANCE 20+ In Stock

-

1

+

C\$359²⁷

ADD TO CART

Volume Pricing	
Qty 1+	C\$359.27 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Thickness: 0.70mm
Material: Si

Compatible Window:

7100350

Lightpath Lens Code:

Physical & Mechanical Properties	
15.10	Clear Aperture CA (mm):
Matte Black Anodized Aluminum Housing	Construction:
18.67	Length (mm):
24.00	Front Diameter (mm):
Optical Properties	
15.00	Effective Focal Length EFL (mm):
Black Diamond™ BD-6	Substrate:
1.0	f/#:
BBAR (8000-12000nm)	Coating:
8000 - 12000	Wavelength Range (nm):
R _{avg} <0.75% @ 8000 - 12,000nm	Coating Specification:
2.7816	Index of Refraction (n _d) @ 10μm:
2.7683	Index of Refraction (n _d) @ 14μm:
2.7978	Index of Refraction (n _d) @ 4μm:
11.24	Working Distance (mm):
Sensor	
384 x 288 / 17μm	Recommended Detector Format (H x V/Pixel Size):
Threading & Mounting	
M25 x 0.5	Mounting Threads:
7.00	Thread Length (mm):
Material Properties	
22.5	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
30.5 x 10 ⁻⁶ @ 10μm	Thermo-optic coefficient dn/dT:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

PRODUCT DETAILS

- Precision Molded Chalcogenide Lenses
- Compact Designs for Thermal Imaging Cameras
- Focal Lengths from 2.7 to 24mm

Lightpath® Thermal Imaging Assemblies are a cost-effective alternative to diamond turned infrared lenses for applications in the mid-wave infrared (MWIR) or long-wave infrared (LWIR). These lenses are molded from BD6™, a chalcogenide glass that offers high transmission from 1 to 15μm and is also optically athermalized from -40 to +85°C. These lenses feature a broadband antireflection coating from 8 to 12μm and are mounted in compact black anodized aluminum housings that are threaded to allow for adjustable focus. Lightpath Thermal Imaging Assemblies are ideal for medical diagnostics, gas sensing, thermography, thermal imaging, security, and manufacturing process control applications. Lenses with focal lengths from 2.7 to 24mm are available, covering detector sizes from 80 x 80 to 640 x 480 pixels.