

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#) / [LUCID Vision Labs Atlas10 10GigE Power over Ethernet \(PoE\) Cameras](#)

[See all 31 Products in Family](#)

LUCID Vision Labs Atlas10 ATX245S-CT, Sony IMX530, 24.5MP, Color Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Atlas10 10GigE Power over Ethernet (PoE) Cameras (Front, C-Mount)



Stock **#17-115** [CONTACT US](#)

- 1 +

C\$6,596.80

ADD TO CART

Qty 1+
C\$6,596.80
Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads
Video Output: 10GigE (PoE+)
Type: Color Camera
Manufacturer:

Lucid Vision Labs
Mounting Threads: 2 x ¼-20 with Tripod Mount Adapter #17-120
Image Buffer: 380MB
Camera Family: Atlas10
Model Number: ATX245S-CT
Imaging Sensor: Sony IMX530
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 4/3"
Resolution (MegaPixels): 24.50
Pixels (H x V): 5,320 x 4,600
Pixel Size, H x V (µm): 2.74 x 2.74
Sensing Area, H x V (mm): 14.58 x 12.60
Frame Rate (fps): 50.60
Pixel Depth: 8/10/12 bit
Exposure Time: 6.97µs - 10s
Connector: 10GigE, M12
Power Supply: Power Supply Required and Sold Separately. USA: #18-364 Europe: #18-364 Japan: #18-364 Korea: Not Available China: #18-364
Power Consumption (W): 11.5 (External Power Supply) <12 (PoE+)
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports
Synchronization: Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)
Dimensions (mm): 55 x 55 x 95.5 (excludes connectors and lens mount)
Weight (g): 304
Mount: TFL-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 70.63
Operating Temperature (°C): -20 to +55
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 8-pin M8
Machine Vision Standard: GigE Vision v2.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

