

LUCID Vision Labs Triton™ TRI050S-PC, Sony IMX250MZR, 5.0MP, Polarized Monochrome Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Triton™ Power over Ethernet (PoE) Cameras



Stock **#13-723** ☐ In Stock

[Similar Cameras](#)

⊖ 1 ⊕

C\$3,053.40

ADD TO CART

Qty 1+

C\$3,053.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Polarized Monochrome Camera

Manufacturer: Lucid Vision Labs
Mounting Threads: ¼-20 with Tripod Mount Adapter #11-474
Image Buffer: 128MB
Camera Family: Triton™
Model Number: TRI050S-PC
Imaging Sensor: Sony IMX250MZR
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 5.00
Pixels (H x V): 2,448 x 2,048
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 8.45 x 7.07
Frame Rate (fps): 24.00
Pixel Depth: 12 bit
Exposure Time: 30µs - 10s
Connector: GigE, M12
Power Supply: Power Supply Required and Sold Separately: USA: #18-364 Europe: #18-364 Japan: #18-364 Korea: Not Available China: #18-364
Power Consumption (W): 2.5 (External Power Supply) 3.1 (PoE)
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports
Synchronization: Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)
Dimensions (mm): 29 x 29 x 45 (excludes connectors and lens mount)
Weight (g): 67
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 71.34
Operating Temperature (°C): -20 to +55
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 8-pin M8
Machine Vision Standard: GigE Vision v2.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

