

[See all 65 Products in Family](#)

# IDS Imaging U3-3884LE-C-HQ-VU 1/1.8" Color USB3 Camera Rev. 1.2 (Recertified 05-P)

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (C/CS - Mount, Full Housing, Front View)



Stock #78-149-RCD-05P RECERTIFIED **1 In Stock**

C\$365<sup>54</sup>

ADD TO CART

**Volume Pricing**

Qty 1+	C\$365.54 each
Need More?	<a href="#">Request Quote</a>

**Product Downloads**

**Color**                      **Spectrum:**

**General**

**Color Camera**                      **Type:**

**Sensor**

**1/1.8"**                      **Sensor Format:**

6.40	<b>Resolution (Megapixels):</b>
54.00	<b>Frame Rate (fps):</b>
3,088 x 2,076	<b>Pixels (H x V):</b>
2.40 x 2.40	<b>Pixel Size, H x V (µm):</b>
Sony IMX178	<b>Imaging Sensor:</b>
Rolling	<b>Shutter Type:</b>

## Hardware & Interface Connectivity

Vertical	<b>Connector:</b>
----------	-------------------

## Threading & Mounting

C-Mount	<b>Mount:</b>
---------	---------------

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- Up to 8.0MP Resolution with Framerrates up to 230fps
- Board Level Options with C/CS-Mount or S-Mount Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GenICam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mount or C/CS-Mount versions. The C/CS-Mount configurations come with a 5mm spacer to easily adapt between C-Mount and CS-Mount lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.

## Calibration Services

;