

Coherent® LightSmyth™ 1030nm, 1600 Grooves/mm, 120 x 20mm Transmission Diffraction Grating

See More by [Coherent®](#)



LightSmyth™ Transmission Diffraction Gratings

Stock **#16-865** ☐ In Stock

-

1

+

C\$5,992.00

ADD TO CART

Qty 1+
C\$5,992.00
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm): 1600
Groove Density Uniformity (grooves/mm): 0.001
Design Wavelength DWL (nm): 1030 ±10

Minimum Efficiency (%) : ≥94 @ 1030nm
Dimensions (mm) : 120.00 x 20.00
Angle of Incidence (°) : 55.5 ±1
Clear Aperture CA (mm) : 115.00 x 18.00
Coating : Dielectric
Construction : Multi-Layer Dielectric Binary Etch Grating
Length (mm) : 120.00
Model Number : 1304189
Substrate :  Fused Silica (Corning 7980)
Surface Quality : 60-40
Thickness (mm) : 0.95 ±0.050
Type : Transmission Diffraction Grating
Width (mm) : 20.00
Alignment of Grooves to Edge (°) : 0.1 (typical)
Polarization : S
Note : S-Polarization defined with E-field parallel to the grating grooves

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View