

[See all 13 Products in Family](#)

## M72 x 0.75 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock #22-785 **20+ In Stock**

⊖ 1 ⊕ C\$102<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | C\$102.90 each                |
| Qty 10-25      | C\$97.30 each                 |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

### General

Mounted Imaging Filter **Type:**

### Physical & Mechanical Properties

68.00 **Clear Aperture CA (mm):**

74.50 **Diameter (mm):**

**Construction:**

Dichroic

## Optical Properties

Uncoated  
Coating:  
Extinction Ratio:  
Approx. 19:1 at 400nm  
Approx. 200:1 at 500nm  
≥2700:1 at 550-650nm  
Approx. 600:1 at 700nm

Float Glass  
Substrate: □  
Polarization:  
95% Efficiency

Single: 30  
Crossed: 0.15  
Transmission (%):  
Wavelength Range (nm):  
400 - 700

## Threading & Mounting

M72 x 0.75  
Filter Thread:  
Mount Thickness (mm):  
9  
Mount Thickness Including Threads (mm):  
11

## Environmental & Durability Factors

Operating Temperature (°C):  
-15 to +70

## Regulatory Compliance

View  
Certificate of Conformance:

## Product Details

- Stackable, Rotating Mount for Easy Integration into Imaging Systems
- Eliminate Hot Spots and Reduce Glare
- 95% Polarization Efficiency
- Also Available [Unmounted](#)

Mounted Linear Glass Polarizing Filters feature a rotatable threaded mount available in a wide range of standard thread sizes. Linear polarizing filters will transmit a single axis of polarization and can be used to reduce glare and hot spots in imaging systems. Two polarizing filters can be stacked to achieve a variable density effect. Thickness includes a 2mm male thread. Mounted Linear Glass Polarizing Filters have 95% polarization efficiency. The filters are also available [unmounted](#).

## Technical Information

