

[See all 17 Products in Family](#)

## InGaAs FC Fiber Balanced Photoreceiver, 900-1700nm



Stock #90-641 **NEW** [CONTACT US](#)

- 1 + C\$5,347<sup>50</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$5,347.50 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Note:**

Includes:  
Lemo®3-pin connector  
(3) Adapter SMA (male) to BNC (female)  
Datasheet

### Physical & Mechanical Properties

**Weight (g):**

350

**Dimensions (mm):**

Case Size: 80 x 80 x 30.5

## Optical Properties

900 - 1700 nm **Spectral Range:**

## Sensor

InGaAs PIN photodiode **Detector Type:**

## Electrical

$2 \times 10^4$  or  $6 \times 10^4$ (switchable) **Transimpedance Gain ( $\Omega$ ):**

$4 \times 10^{-12}$  @880nm **Noise Equivalent Power NEP ( $W/Hz^{1/2}$ ):**

100 MHz **Bandwidth (-3 db):**

$\pm 1.0$  V at 50  $\Omega$  load (for linear gain and low harmonic distortion), maximum  $\pm 2.0$  V at 50  $\Omega$  load **Output Signal:**

$20 \times 10^3$  or  $57 \times 10^3$ (switchable) **Conversion Gain ( $V/W$ ):**

55 **Common Mode Rejection (dB):**

## Hardware & Interface Connectivity

$\pm 15$  V ( $\pm 14.5$  V...  $\pm 16.5$  V) -90 / +120 mA **Power Requirement:**

Power Supply Required and Sold Separately.  
USA: [#59-180](#)  
Europe: [#59-180](#)  
Japan: Not Available  
Korea: Not Available  
China: [#59-180](#) **Power Supply:**

## Environmental & Durability Factors

0 to +60 **Operating Temperature ( $^{\circ}C$ ):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

## Product Details

- Subtracts Two Photodiode Signals for Differential Detection
- Improved Signal to Noise Ratio (SNR) for Weak or Modulated Optical Signals
- High Common-Mode Noise Suppression for Improved Measurement Sensitivity and Accuracy
- Available in Si and InGaAs models for UV-VIS and NIR spectral ranges

Balanced Photoreceivers use true differential detection by subtracting the photocurrents from two matched photodiodes, producing a single electrical output proportional to the difference in optical power between the two inputs. This suppresses common-mode noise, such as laser intensity fluctuations, improving SNR and measurement sensitivity. Balanced Photoreceivers are engineered with a low-noise transimpedance amplifier, which ensures stable, consistent performance for precision optical measurements. Available in Si and InGaAs models for UV-VIS (320-1000nm) and NIR (800-1700nm) spectral ranges, these photoreceivers are ideal for coherent optical detection, interferometry, spectroscopy, and optical coherence tomography (OCT).

**Note:** Power supply sold separately. Please see specifications for more details.