

[See all 43 Products in Family](#)

Model 1101P, 1.5mW Linear Polarization, Lumentum HeNe Laser



Lumentum High Performance Helium-Neon Lasers



Stock **#62-719** 1 In Stock

-

1

+

C\$1,687⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,687.00 each
Need More?	Request Quote

Product Downloads



General

10	Warm-Up Time (minutes):
Lumentum	Manufacturer:
HeNe	Type of Laser:
IIIa	Laser Class - CDRH:

1101P	Model Number:
Physical & Mechanical Properties	
N/A	Pointing Stability after Warm Up (mrad°C):
0.54	Weight (lbs):
9.50	Length of Laser Head (inches):
Centered to Outer Cylinder: ±0.01" Parallel to Outer Cylinder: ±1.0 mrad	Static Alignment:
N/A	Pointing Stability (mrad°C):
1.245	Diameter of Laser Head (inches):
Optical Properties	
500:1	Polarization:
TEM ₀₀	Spatial Mode:
632.80	Wavelength (nm):
±3	Beam Diameter Tolerance (%):
±3	Beam Divergence Tolerance (%):
Mean Power over 8 hrs: ±2.5	Maximum Drift:
0.63	Beam Diameter (mm):
1.30	Beam Divergence (mrad):
Red	Color:
>95%	Mode Purity (TEM ₀₀):
Electrical	
1.5	Output Power (mW):
30 Hz - 10 MHz 0.1%	RMS Noise:
730	Longitudinal Mode Spacing, Nominal (MHz):
1.5	Minimum Output Power, TEM ₀₀ (mW):
Hardware & Interface Connectivity	
Power Supply: #11-380 (110/220V AC), #11-384 (12VDC), #11-385 (24VDC), #11-387 (110/220V AC)	
Free Space	Output Type:
Environmental & Durability Factors	
-40 to +70	Operating Temperature (°C):
0 to 100%, non-condensing	Operating Humidity:
-40 to +150	Storage Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

110V or 220V power supplies sold separately. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993.

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

