

[See all 14 Products in Family](#)

LightPath 390036 | 6.5mm Dia., 0.56 NA, BBAR (3000-5000nm), Mounted IR Aspheric Lens

See More by [Lightpath®](#)



Stock #66-569 **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ C\$574⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	C\$574.00 each
Qty 11-49	C\$516.60 each
Need More?	Request Quote

Product Downloads

General

390036 **Lightpath Lens Code:**

Aspheric Lens **Type:**

Physical & Mechanical Properties

6.50 ±0.10 **Diameter (mm):**

5.00	Clear Aperture CA (mm):
2.50	Center Thickness CT (mm):
Protective as needed	Bevel:
Optical Properties	
4.00 @ 2500nm	Effective Focal Length EFL (mm):
0.56	Numerical Aperture NA:
Black Diamond™ BD-2 (Ge ₂₆ Sb ₁₂ Se ₆₀)	Substrate: <input type="checkbox"/>
2500	Aspheric Design Wavelength (nm):
BBAR (3000-5000nm)	Coating:
R _{avg} <1.0% @ 3 - 5μm	Coating Specification:
80-50	Surface Quality:
0.89	f#:
2.6023	Index of Refraction (n_d) @ 10μm:
2.5843	Index of Refraction (n_d) @ 14μm:
2.6210	Index of Refraction (n_d) @ 4μm:
2.6173	Index of Refraction (n_d) @ 5μm:
3000 - 5000	Wavelength Range (nm):
3.05	Working Distance (mm):
Infinite	Conjugate Distance:
2500	Focal Length Specification Wavelength (nm):

Threading & Mounting

Stainless Steel, M9 x0.5 Thread	Mount:
---------------------------------	---------------

Material Properties

14.00	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
4.68	Density (g/cm³):
70 x 10 ⁻⁶ /°C from -40° to +80°C (5 - 14 μm)	Thermo-optic coefficient dn/dT:
285.00	Transformation Temperature (°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Wavelength Range of 1.8 - 12μm
- Variety of Coating Options
- Mounted and Unmounted Versions

LightPath® Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses feature a low-cost, molded design and offer several key benefits over Germanium substrate aspheres. With a dn/dT and CTE significantly less than that of Germanium, the lenses feature a smaller change in focal length as a function of temperature change. Featuring a higher operating temperature than Germanium (which suffers 20 – 30% transmission loss at 100°C), the lenses can be used in applications including collimators for QCL lasers and as components within thermal imaging assemblies. LightPath Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses have a wavelength range of 1.8 - 12μm. These lenses are available mounted or unmounted, in a variety of coating options.

Technical Information

