

[See all 14 Products in Family](#)

# LightPath 390037 | 5.5mm Dia., 0.85 NA, BBAR (1800-3000nm), Mounted IR Aspheric Lens

See More by [Lightpath®](#)



Stock #66-572 CLEARANCE **2 In Stock**

[Other Coating Options](#)

C\$352<sup>43</sup>

ADD TO CART

Volume Pricing	
Qty 1+	C\$352.43 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

390037 **Lightpath Lens Code:**

Aspheric Lens **Type:**

**Physical & Mechanical Properties**

5.50 ±0.10 **Diameter (mm):**

4.00 **Clear Aperture CA (mm):**

3.00	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>
<b>Optical Properties</b>	
1.87 @ 9500nm	<b>Effective Focal Length EFL (mm):</b>
0.85	<b>Numerical Aperture NA:</b>
Black Diamond™ BD-2 (Ge <sub>28</sub> Sb <sub>12</sub> Se <sub>60</sub> )	<b>Substrate:</b> <input type="checkbox"/>
9500	<b>Aspheric Design Wavelength (nm):</b>
BBAR (1800-3000nm)	<b>Coating:</b>
R <sub>avg</sub> < 1.0% @ 1.8 - 3.0μm	<b>Coating Specification:</b>
80-50	<b>Surface Quality:</b>
0.58	<b>f#:</b>
2.6023	<b>Index of Refraction (n<sub>d</sub>) @ 10μm:</b>
2.5843	<b>Index of Refraction (n<sub>d</sub>) @ 14μm:</b>
2.6210	<b>Index of Refraction (n<sub>d</sub>) @ 4μm:</b>
2.6173	<b>Index of Refraction (n<sub>d</sub>) @ 5μm:</b>
1800 - 3000	<b>Wavelength Range (nm):</b>
0.72	<b>Working Distance (mm):</b>
Infinite	<b>Conjugate Distance:</b>
9500	<b>Focal Length Specification Wavelength (nm):</b>

## Threading & Mounting

Stainless Steel, M9 x 0.5 Thread	<b>Mount:</b>
----------------------------------	---------------

## Material Properties

14.00	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>
4.68	<b>Density (g/cm<sup>3</sup>):</b>
70 x 10 <sup>-6</sup> /°C from -40° to +80°C (5 - 14 μm)	<b>Thermo-optic coefficient dn/dT:</b>
285.00	<b>Transformation Temperature (°C):</b>

## Regulatory Compliance


<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 233:</b>

## Product Details

- Wavelength Range of 1.8 - 12μm
- Variety of Coating Options
- Mounted and Unmounted Versions

LightPath® Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses feature a low-cost, molded design and offer several key benefits over Germanium substrate aspheres. With a dn/dT and CTE significantly less than that of Germanium, the lenses feature a smaller change in focal length as a function of temperature change. Featuring a higher operating temperature than Germanium (which suffers 20 – 30% transmission loss at 100°C), the lenses can be used in applications including collimators for QCL lasers and as components within thermal imaging assemblies. LightPath Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses have a wavelength range of 1.8 - 12μm. These lenses are available mounted or unmounted, in a variety of coating options.

## Technical Information



;