

Irradiance Integrating Sphere

See More by [Ocean Optics](#)



Stock **#90-588** NEW **1 In Stock**

- 1 + **C\$1,953^{.00}**

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,953.00 each
Need More?	Request Quote

Product Downloads

Diameter of Entrance Port (mm):

9.5

General

Model Number:

FOIS-1

Note:

Collects light from emission sources such as LEDs and lasers and is used to measure light fields with a 360° field of view

Physical & Mechanical Properties	
240	Weight (g):
56.8 x 62.4 x 38.1	Dimensions (mm):
38.10	Diameter (mm):
Optical Properties	
Spectralon®	Coating:
250 - 2500 nm	Spectral Range:
Threading & Mounting	
Mounting Threads: Side Mounts: (1)SMA905 connector for coupling optical fiber to the spectrometer(1) 8-32 threaded hole for post mounts Top Cap Mounts: (2) 8-32 (hardware not included)(1) 1/4-20 threaded hole in center (screw/adapter included)	
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Measure Total Irradiance or Reflectance with Models Optimized for Emission Sources or Surface Illumination
- Ideal for UV–NIR Applications in Materials Testing, LEDs, Lasers, and More
- White Reflectance Standard Provides Stable, Repeatable Reference Measurements
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics integrating spheres provide flexible, accurate solutions for measuring light output or surface reflectance across a wide spectral range. Whether you need 360° field-of-view irradiance collection, uniform surface illumination for reflectance measurements, or a stable reference for calibration, these integrating spheres ensure consistent, reliable results. The White reflectance standard ([#90-586](#)) complements the spheres by providing a dependable calibration reference for diffuse reflectance measurements. Ocean Optics Integrating Spheres are well-suited for UV-NIR applications, including material testing, LED analysis, and laser measurements.

Selection Guide:

FOIS-1 ([#90-588](#)): Best for **irradiance measurements** and light emission sources; features a 360° field of view for collecting light from LEDs, lasers, and other broad light fields.

ISP-REF ([#90-587](#)): Best for **surface reflectance measurements**; provides even surface illumination and integrates a transfer optic and built-in light source for easy measurement of color or reflectivity on opaque or directional samples.

WS-1 ([#90-586](#)): Use alongside your integrating sphere for reliable white reference measurements when calibrating for diffuse reflectance.