

**TECHSPEC® Mounting Clamp, 68mm Inner Diameter**



Mounting Clamp, 68mm Inner Diameter, #56-024

Stock **#56-024** **13 In Stock**

⊖ 1 ⊕ C\$351<sup>00</sup>

**ADD TO CART**

Volume Pricing

Qty 1+	C\$351.40 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Lens Accessory **Type:**

**Physical & Mechanical Properties**

68.0 **Inner Diameter (mm):**

**Optical Properties**

VS **Lens Wavelength Range:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**Compliant** **Reach 209:**


**View** **Certificate of Conformance:**

## Product Details

- High Resolution Telecentric Lens for Measurement and Gauging
- Up to 5 MegaPixels, 3.45µm Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.06X to 1X


TECHSPEC® GoldTL™ Telecentric Lenses were designed specifically for machine vision and metrology applications. The unique focusable design allows for working distance adjustment, while still providing <math><0.2^\circ</math> telecentricity. These lenses also feature high resolutions, low distortions, and are available for 1/2" or 2/3" sensors. TECHSPEC® GoldTL™ Telecentric Lenses have a front filter thread for easy integration of [color filters](#), [polarizers](#) or other mounted components. Both the iris and focusing adjustment positions can be fixed by set screws to remain secure in high vibration environments.

## Technical Information




**0.08X & 0.06X Telecentric Lens**

Units: mm




**1X & 0.73X Telecentric Lenses**

Units: mm



**0.5X & 0.36X Telecentric Lenses**



**0.25X & 0.18X Telecentric Lenses**

Units: mm

Stock No.	A	B	C	D	E	F	G
<a href="#">#56-024</a>	88mm	16mm	34mm	94mm	120mm	101.6mm	50mm
<a href="#">#56-025</a>	85mm	17.5mm	32.5mm	91mm	120mm	101.6mm	48.5mm
<a href="#">#56-026</a>	103mm	—	39.5mm	107mm	103mm	90mm	55.5mm
<a href="#">#56-027</a>	134mm	—	55mm	148mm	134mm	122mm	81mm

