

MT-L Accessory Tube Lens

See More by [Mitutoyo](#)



Stock **#56-073** **3 In Stock**

-

1

+

C\$3,129⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$3,129.00 each
Need More?	Request Quote

Product Downloads

General

MT-L	Model Number:
Tube Lens	Type:

Physical & Mechanical Properties

35.00	Diameter (mm):
32.00	Length (mm):

Optical Properties	
200.00	Focal Length FL (mm):
1X	Magnification:
355 - 1800	Wavelength Range (nm):
24.00	Field Number (mm):
22.00	Entrance Pupil Diameter (mm):
Threading & Mounting	
M32 x0.5 pitch	Mounting Threads:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Creates an Image When Used With a Mtutoyo Objective
 - Low Cost Alternative to [Mitutoyo VMU](#) and [FS-70 Microscopes](#)
 - [Accessory Adapters](#) Available to Ease Integration with C-Mount Cameras
- Mitutoyo Tube Lenses function as secondary lenses to form an image using any of the [Mitutoyo Infinity Corrected Objectives](#), They are economical alternatives to the [FS70 Microscope](#) or [Infinitube® In-line Assembly Unit](#). Several options are available, depending upon system requirements. The MT-4 and MT-40 are designed for end-user integration and can easily be used with any C-Mount camera with our Mitutoyo C-Mount Camera Extension Tube [#56-992](#). Mitutoyo Tube Lenses MT-4 Tube Lens is recommended for use with Objectives from 1X to 20X magnification, while the MT-40 is recommended for use with Objectives with >20X magnification. The MT-1 Tube Lens permits the introduction of a beamsplitter to the imaging path, allowing for a custom in-line illumination system. The MT-2 Tube Lens is similar to the MT-1 but with an effective focal length of 400mm, providing twice the stated magnification for any of the Mtutoyo objectives. The MT-L and MT-L4 lenses are designed for the [M Plan NUV](#) and [M Plan UV](#) series of objectives, respectively. [NIR and zoom tube lenses](#) are also available through our line of Precision Zoom Lenses.

Technical Information

