

Laser Detection Card NIR



Laser Detection Card NIR, #36-743

Stock **#36-743** **20+ In Stock**

⊖ 1 ⊕ C\$184⁰⁰

ADD TO CART

Volume Pricing

Qty 1-5	C\$184.80 each
Qty 6-24	C\$175.00 each
Need More?	Request Quote

Product Downloads

General

Card **Type:**
Nd:YAG, Fiber Laser **Typical Applications:**

Physical & Mechanical Properties

86 x 54 **Dimensions (mm):**
42 x 23 **Size of Active Area (mm):**

Optical Properties

NIR	Wavelength:
Orange/Red (655nm)	Emission Color:
700 - 1400nm	Stimulation Range:

Electrical

<50 ms	Persistence (Stimulation Removed):
8 $\mu\text{W}/\text{cm}^2$ @ 1064nm	Minimum Stimulation, Continuous:
100 W/cm^2 @ 1064nm (estimated)	Maximum Stimulation, Continuous:
35 MW/cm^2 @ 1064nm, 7ns (estimated)	Maximum Stimulation, Single Pulse:

Regulatory Compliance


Compliant	Reach 191:
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- Full Spectrum Coverage: UV, VIS, IR Series
- 3 Mounted Formats Have Safe, Non-reflective Encapsulation
- Unique, No Pre-charge for IR Detection and No Fading During Use
- Flexibility for Either Transmission or Reflective Viewing





Laser Detection Products offer UV, visible, and IR laser users' greater performance and safety. They reduce problems associated with beam visualization, profiling, and alignment in many applications. Each range is available in three formats. Laser Detection Products' laminated credit card style is for low-power sources and reflective viewing only. The 25mm disk and clip-on wand style is used when frequent component positioning is required. The removable disk is positional at an optics location to enable precise alignment, while the wand format permits handling into the beam path. The optical bench-mountable head format has a large active area and 1/4-20 threaded mounting for standard English post/post holder integration.

Technical Information



NIR Detection Products

Laser Detection Products				
	UV	VIS	IR	NIR
Stimulation Range	250 - 550nm	Band 1: 400 - 640nm Band 2: 800 - 1700nm	Band 1: 790 - 840nm Band 2: 870 - 1070nm Band 3: 1550nm	700 - 1400nm
Typical Applications	HeCd, Ar-Ion, tripled Nd:YAG, etc.	Ar-Ion, HeNe, HeCd, Nd:YAG, etc.	808nm, 820nm, 830nm, 880nm, 960 - 980nm Laser Diodes, Nd:YAG, 1550nm telecommunications	Nd:YAG, Fiber Laser
Emission Color	Yellow (580nm), Broadband (490nm - 700nm)	Orange/Red (655nm), Broadband (600 - 730nm)	Green (550nm), other peaks at Red (673nm) and Blue (400nm)	Orange/Red (655nm)
Persistence (Stimulation Removed)	6 s - 4 mins (dependent on ambient light)	Visible: 0.5 - 3 s (dependent on ambient light) IR: <0.5 s	800 μs	<50 ms
Continuous (Minimum Stimulation)*	<1 nW/cm^2 @ 450nm & 365nm	<1 nW/cm^2 @ 450nm <25 $\mu\text{W}/\text{cm}^2$ @ 950nm	<2 $\mu\text{W}/\text{cm}^2$ @ 808nm <175 nW/cm^2 @ 960nm <100 $\mu\text{W}/\text{cm}^2$ @ 1550nm	8 $\mu\text{W}/\text{cm}^2$ @ 1064nm

Pulsed (Minimum Stimulation)*	$8\text{W}/\text{cm}^2$ @ 337nm, 4ns, 20Hz, $40\text{W}/\text{cm}^2$ @ 337nm, 4ns, 1Hz	2 kW/cm ² @ 1064nm, 7ns, 10Hz	250 kW/cm ² @ 1064nm, 7ns, 10Hz	N/A
Continuous (Maximum Stimulation)	100W/cm ² @ 512nm (all formats)	100W/cm ² @ 512nm (all formats)	100W/cm ² (all formats)	100W/cm ² @ 1064nm (estimated)
Single Pulse (Maximum Stimulation)	130MW/cm ² @ 337nm, 4ns (card only) 850MW/cm ² @ 337nm, 4ns (other formats) 60MW/cm ² @ 1064nm, 7ns (all formats)	130MW/cm ² @ 337nm, 4ns (card only) 850MW/cm ² @ 337nm, 4ns (other formats) 60MW/cm ² @ 1064nm, 7ns (all formats)	35MW/cm ² @ 1064nm, 7ns (all formats)	35MW/cm ² @ 1064nm, 7ns (estimated)
				

*Measured in darkened conditions