

[See all 15 Products in Family](#)

Laser Safety Window LS25 ARW 304.8 x 304.8mm



Laser Safety Windows

Stock #75-516 **NEW** 2 In Stock

⊖ 1 ⊕ C\$250⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$250.60 each
Qty 6-10	C\$225.54 each
Need More?	Request Quote

Product Downloads

General

EN 207/208 Ratings:

D AB7 + IR AB3 190– 315
 D AB5 + IR AB7 + MAB7Y >315– 515
 D AB5 + IR AB6 + MAB6Y >515– 526
 DIR AB5 + MAB5Y >526–532
 DIR AB4 + MAB4Y >532 – 535
 DI AB2 10600

Filter Material:

Polymer

Filter:

LS25

Physical & Mechanical Properties

304.8 x 304.8 **Dimensions (mm):**

3.00 **Thickness (mm):**

Optical Properties

Optical Density OD (Average):
>7 @ 190-515
>6 @ 516-525
>5 @ 526-532
>4 @ 533-535
>5 @ 10600

Orange **Color:**

41 **Visible Light Transmission VLT (%):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- CE Certified Laser Radiation Protection
- Available for UV, VIS, and NIR Wavelengths
- 200mm x 100mm Size Ideal for Small Enclosures
- 304.8mm x 304.8mm Sizes Also Available

Laser Safety Windows feature high optical density in a specified wavelength range across the UV, VIS, and NIR spectra. Made from acrylic and polycarbonate, these laser safety windows are CE certified to protect against laser radiation. These windows are available in 200 x 100mm for easy integration into small equipment doors, windows, and enclosures. 304.8 x 304.8mm sizes are also available. Laser Safety Windows are ideal for blocking laser radiation while providing safe viewing of laser environments in materials processing, manufacturing, and laboratory applications featuring Nd:YAG, CO₂, fiber, and other laser sources.

Warning: Because of the potential for eye damage, the degree of protection required in each circumstance should be determined by the Laser Safety Officer, the industrial hygienist, or the individual responsible for the safety program.