

NIR Wire Grid Polarizer, HT, 700nm-2500nm, 50 x 35mm Dia



Photo shows 26-998 and 27-000 NIR Wire Grid Polarizers

Stock **#27-004** CLEARANCE **2 In Stock**

-

1

+

C\$2,184⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$2,184.00 each
Qty 6+	C\$1,960.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

Linear Polarizer

Physical & Mechanical Properties

Clear Aperture CA (mm):

46 x31	
50 x35 ±0.2	Dimensions (mm):
1.53 ±0.2	Thickness (mm):
Wire Grid	Construction:
Optical Properties	
0° ±20°	Angle of Incidence (°):
Uncoated	Coating:
150:1@900nm 500:1@1400nm 800:1@1900nm 1000:1@2400nm	Extinction Ratio:
Wire Grid on Display Grade Glass	Substrate:
80-50	Surface Quality:
>88.1@900nm >91.0@1400nm >91.3@1900nm >90.3@2400nm	Transmission (%):
700 - 2500	Wavelength Range (nm):
Threading & Mounting	
Unmounted	Mount:
Material Properties	
31.7 x 10-7/°C (0 - 300°C)	Thermal Expansion:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Designed for 700 - 2500nm
- High Transmission and High Contrast Versions Available
- Ideal for Thermal Imaging

NIR Wire Grid Polarizers are broadband polarizers designed to provide high transmission from 700 - 2500nm. These polarizers are optimized as either a high contrast version, providing 5900:1 extinction ratio at 2400nm, or as a high transmission version providing up to 91% transmission at 1900nm. NIR Wire Grid Polarizers are manufactured on high-grade display glass, providing excellent heat resistance for NIR applications. When incident light strikes the wire grid, P-polarized light contacts a dielectric and is transmitted, while S-polarized light contacts a mirror and is reflected.

SPECIAL HANDLING

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools