

[See all 48 Products in Family](#)

## Norland Optical Adhesive NOA 1622H, 1 oz. Application Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA 1622H, 1 oz. Application Bottle

Stock **#17-360** [CONTACT US](#)

⊖ 1 ⊕ **C\$157<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1-4	<b>C\$157.50</b> each
Qty 5-11	<b>C\$147.00</b> each
Qty 12+	<b>C\$141.00</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

1 **Size (oz):**

1622H **Norland Number:**

4 months **Shelf Life:**

**Type:**

Bottle

**Typical Applications:**  
Bonding glass to glass

**Note:**  
Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure. Liquid adhesives cannot be put in a vacuum because it will remove the stabilizers and sensitizers causing the adhesive to not cure properly. **This adhesive should be refrigerated between 5 - 10°C when stored to maintain its optical properties.**

**Cure:**  
UV/Heat

## Optical Properties

**Index of Refraction ( $n_d$ ):**  
1.622 @ 589nm

**Absorption Range (nm):**  
315 - 395

## Material Properties

**Glass Bonding:**  
Excellent

**Metal Bonding:**  
Excellent

**Plastic Bonding:**  
Excellent

**Viscosity (cps):**  
220

**Bonding Type:**  
Glass to Glass

**Energy for Full Cure ( $J/cm^2$ ):**  
6

## Environmental & Durability Factors

**Durability:**  
Soft & Flexible

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 251:**  
[Compliant](#)

## Product Details

- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

Norland Optical Adhesives are clear, solvent-free optical adhesives designed to fully cure in only minutes when exposed to ultraviolet light. These adhesives are used in precision alignment or positioning applications that require a robust and resilient bond. Norland Optical Adhesives feature a variety of bonding types, including but not limited to glass to glass, glass to glass/metal, and plastic to plastic/glass. To use Norland Optical Adhesives, apply the adhesive to the optical surface, position the components, and use a [UV light source](#) to set the components in place. Since the adhesive will not cure until exposed to UV light, time can be taken during the positioning process to perfect product alignment.

## Technical Information

**NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES**

Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.