

# Coherent® OBIS™ FP 1193825 | 405nm LX 50mW Laser, Fiber Pigtail, FC

See More by [Coherent®](#)



Coherent® High Performance OBIS™ Fiber-Pigtailed Laser Systems



Stock **#88-028** **1 In Stock**

⊖ 1 ⊕ C\$10,017<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | C\$10,017.00 each             |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads



### General

|               |                                |
|---------------|--------------------------------|
| <5            | <b>Warm-Up Time (minutes):</b> |
| 3mm Mono-Coil | <b>Fiber Cable Type:</b>       |
| Coherent®     | <b>Manufacturer:</b>           |
|               | <b>Type of Laser:</b>          |

Diode

IIIb **Laser Class - CDRH:**

1193825 **Model Number:**

## Optical Properties

100:1 **Polarization:**

TEM<sub>00</sub> **Spatial Mode:**

405.00 ±5 **Wavelength (nm):**

≤1.1 **Mode Quality, M<sup>2</sup>:**

Violet **Color:**

0.05 **Fiber Numerical Aperture NA (1/e<sup>2</sup>):**

## Electrical

50 **Output Power (mW):**

<2 **Power Stability (%):**

Digital: 150 **Modulation Frequency (MHz):**

Analog: 500 **Modulation Frequency (kHz):**

≤0.2% (20Hz to 20MHz) **RMS Noise:**

## Hardware & Interface Connectivity

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#87-473](#)  
Europe: [#87-473](#)  
Japan: [#87-473](#)  
Korea: [#87-473](#)  
China: [#87-473](#)

FC/APC; 8° angled **Output from Fiber:**

Fiber-Coupled **Output Type:**

## Environmental & Durability Factors

10 to 50 **Operating Temperature (°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

## Product Details

A power supply is required for operation and sold separately. OBIS remote is required for CDRH certified systems. The OBIS heat sink is recommended.

- High Performance OBIS™ LXLS Lasers with Added Fiber Optic Capability
- Permanent Fiber Attachment Extends Lifetime with Guaranteed Power
- Single-Mode Polarization-Maintaining Fiber with an FC/APC Connector Provide High-Quality and Low-Noise Laser Beam Output
- [Coherent® High Performance OBIS™ LXLS Laser Systems](#) Also Available

Coherent® High Performance OBIS™ LXLS Fiber-Pigtailed Laser Systems are plug-and-play lasers available in wavelengths from the ultraviolet to the near-infrared with an added fiber attachment. The fiber optic is permanently attached to the laser, providing an extended lifetime of the fiber and guaranteed power consistency. An FC/APC connector terminates the fiber to enable connections to other systems without concern for high noise interference. Coherent® High Performance OBIS™ LXLS Fiber-Pigtailed Laser Systems produce high-quality, low-noise laser beams and also allow for hands-free operation. These fiber-pigtailed lasers are used in confocal microscopy, DNA sequencing, polymerase chain reaction (PCR) diagnostic instruments, flow cytometry, medical imaging, and instrumentation applications.

### OBIS Laser System Startup Guide

This downloadable PDF provides guidance on interfacing with OBIS controllers and power supplies, mounting and connecting the heatsink, and starting modulation.

[Download Startup Guide](#)