

MicroBrite 100mm White Line Light



Stock #74-225 NEW CONTACT US

-
1
+
C\$1,078⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$1,078.00 each
Need More?	Request Quote

Product Downloads

General

Type of Illumination:
LED Illuminator

Note:
Compatible with #18-645 external controller

Manufacturer:
Advanced Illumination

Geometry:
Line Light

Illumination Mode:
Constant

Physical & Mechanical Properties

Length (mm):
100.00

Dimensions (mm):
123.7 L x 101.6 W x 20.1 D

Weight (g):
508

Optical Properties

Color:
White

Working Distance (inches):
0.5-23

Hardware & Interface Connectivity

Connector:
Flying Leads

Operating Voltage (V):
24VDC, 1A

Power Supply:
Power Supply Required and Sold Separately:
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

Threading & Mounting

Mount:
M4 Mounting Screws

Environmental & Durability Factors

Operating Temperature (°C):
0 °C to 35 °C

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Contains SVHC\(s\)](#)

Product Details

- Ideal For Line Scan Applications
- High Power LEDs in White, Red, and Blue
- Compact Form Factor for Easy Integration

The Advanced Illumination Microbrite™ Line Lights offer a compact solution for line scan applications. These lights are designed with a high intensity illumination profile and high thermal efficiency, enabling a long lifespan even with continuous operation. These illuminators feature an M4 mounting channel for ease of integration and are available in white, blue, and red wavelengths. The Advanced Illumination Microbrite™ Line Lights are ideal for line scan applications such as high speed inspection of materials including textiles, paper, or plastics and inspection of solar panels or LCDs.

[3D-Printable Mount Files](#)



Bar or Line Light Configuration

[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



Application Note

Illumination Mounts for Machine Vision Applications

[Read](#)



Video

Assembly of 3D Printed Mounts for Common Illumination Geometries

[Watch](#)