

[See all 42 Products in Family](#)

Power Supply for 1.5-2.0mW HeNe Laser, 12 VDC, Bare Wire Leads



L28 Series with CDRH Delay HeNe Laser Power Supply

Stock #11-384 [CONTACT US](#)

- 1 + C\$490.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$490.00 each
Need More?	Request Quote

Product Downloads



General

OEM **Type:**

Compatible Laser Models:
1101, 1101P, 1103, 1103P, 1122, 1122P

L23 Series **Model Number:**

Compatible Laser Stock Number:
#62-718, #62-719, #62-720, #62-721, #64-103,
#64-104

Features:

CDRH Delay (3-5 seconds)

Physical & Mechanical Properties

4.00 x 1.50 x 1.00 **Dimensions (inches):**

Electrical

8.33 **Output Power (W):**

3 (Max. Current Draw) **Input Current (A):**

Hardware & Interface Connectivity

1700 **Output Voltage (V):**

4.9 **Output Current (mA):**

High Voltage Alden Connector **Connector:**

10-14 DC **Input Voltage (V):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

