

[See all 42 Products in Family](#)

Power Supply for 5-7mW HeNe Laser, 12 VDC, Advanced



SL23120 Series HeNe Laser Power Supply

Stock **#18-969** **1 In Stock**

⊖ 1 ⊕ C\$634⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$634.20 each
Need More?	Request Quote

Product Downloads



General

OEM **Type:**

Compatible Laser Models:
[1125](#), [1125P](#), [1137](#), [1137P](#)

Note:
Advanced power supplies include an active filter to reduce current ripple and noise. Additional heat sinking is not required.

L23 Series **Model Number:**

Compatible Laser Stock Number:
#62-722, #62-723, #62-724, #62-725

Physical & Mechanical Properties

4.25 x 3.30 x 1.20 Dimensions (inches):

Electrical

2.5-25 Output Power (W):

5.1 (Max. Current Draw) Input Current (A):

Hardware & Interface Connectivity

2300 Output Voltage (V):

6 Output Current (mA):

High Voltage Alden Connector Connector:

10-14 DC Input Voltage (V):

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

