

[See all 4 Products in Family](#)

Multi-Grid Standard Stage Micrometer on Opal Glass



Stock #59-278 [CONTACT US](#)

- 1 + C\$875⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$875.00 each
Qty 5+	C\$832.58 each
Need More?	Request Quote

Product Downloads

General

NIST Certification:

No

Physical & Mechanical Properties

Scale Divisions:

0.5mm (25µm divisions), 1.0mm (50µm divisions),
2.0mm (100µm divisions), 4.0mm (200µm
divisions), angle grid (15° segments)

Dimensions (mm):

25.4 x 76.2

1.50 ±0.100 **Thickness (mm):**

±0.100 **Dimensional Tolerance (mm):**

Optical Properties

Chrome on Opal Glass **Substrate:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**

Product Details

- Calibrate Distortion in High Magnification Systems

The Multi-Grid Stage Micrometer features grids of varying frequency, and is ideal for calibrating distortion in microscopic systems. Grid sizes are 0.5mm (25µm divisions), 1.0mm (50µm divisions), 2.0mm (100µm divisions) and 4.0mm (200µm divisions). Micrometer also features an angle grid (15° segments). Target is chrome on glass, 1" x 3" x 1.5mm.