

[See all 9 Products in Family](#)

NIR Wire Grid Polarizer, HC, 700nm-2500nm, 25mm x 25mm



Photo shows 26-998 and 27-000 NIR Wire Grid Polarizers

Stock **#26-995** CLEARANCE **2 In Stock**

⊖ 1 ⊕ C\$1,218.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | C\$1,218.00 each |
| Qty 6+ | C\$1,099.00 each |
| Need More? | Request Quote |

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

19 x 19 **Clear Aperture CA (mm):**

25 x 25 ±0.2 **Dimensions (mm):**

Thickness (mm):

5.80 ±0.2 (with mount)

Construction:

Wire Grid

Optical Properties

Angle of Incidence (°):

0° ±20°

Coating:

Uncoated

Extinction Ratio:

1100:1@900nm
3000:1@1400nm
5500:1@1900nm
5900:1@2400nm

Substrate:

Wire Grid on Display Grade Glass

Surface Quality:

80-50

Transmission (%):

>81.5@900nm
>87.7@1400nm
>88.9@1900nm
>88.6@2400nm

Wavelength Range (nm):

700 - 2500

Threading & Mounting

Mount:

Mounted 6061 Anodized Aluminium

Material Properties

Thermal Expansion:

31.7 x 10⁻⁷/°C (0 - 300°C)

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Designed for 700 - 2500nm
- High Transmission and High Contrast Versions Available
- Ideal for Thermal Imaging

NIR Wire Grid Polarizers are broadband polarizers designed to provide high transmission from 700 - 2500nm. These polarizers are optimized as either a high contrast version, providing 5900:1 extinction ratio at 2400nm, or as a high transmission version providing up to 91% transmission at 1900nm. NIR Wire Grid Polarizers are manufactured on high-grade display glass, providing excellent heat resistance for NIR applications. When incident light strikes the wire grid, P-polarized light contacts a dielectric and is transmitted, while S-polarized light contacts a mirror and is reflected.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools