

[See all 48 Products in Family](#)

Norland Optical Adhesive NOA 89H, 1 oz. Application Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA89H, 1 oz Application Bottle

Stock **#17-351** **5 In Stock**

-

1

+

C\$126^{.70}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$126.70 each
Qty 5-11	C\$114.10 each
Qty 12+	C\$108.50 each
Need More?	Request Quote

Product Downloads

General	
1	Size (oz):
89H	Norland Number:
4 months	Shelf Life:
	Type:

Bottle	
Typical Applications:	
Bonding glass to glass	
Note:	
Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure. Liquid adhesives cannot be put in a vacuum because it will remove the stabilizers and sensitizers causing the adhesive to not cure properly.	
Optical Properties	
Index of Refraction (n _d):	
1.51 @ 589nm	
Absorption Range (nm):	
310 - 395	
Material Properties	
Glass Bonding:	
Excellent	
Metal Bonding:	
Good	
Plastic Bonding:	
Fair	
Viscosity (cps):	
15 - 20	
Bonding Type:	
Glass to Glass	
Energy for Full Cure (J/cm ²):	
3.5	
Environmental & Durability Factors	
Durability:	
Soft	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 251:	
Compliant	

Product Details

- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

Norland Optical Adhesives are clear, solvent-free optical adhesives designed to fully cure in only minutes when exposed to ultraviolet light. These adhesives are used in precision alignment or positioning applications that require a robust and resilient bond. Norland Optical Adhesives feature a variety of bonding types, including but not limited to glass to glass, glass to glass/metal, and plastic to plastic/glass. To use Norland Optical Adhesives, apply the adhesive to the optical surface, position the components, and use a [UV light source](#) to set the components in place. Since the adhesive will not cure until exposed to UV light, time can be taken during the positioning process to perfect product alignment.

Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
Applying Adhesive	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
Chemical Resistance of NOA	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
Preventing Lens Separations with NOA	Covers best practices to avoid adhesive failures when bonding optical elements.
Separating Lenses Bonded with NOA	Covers how to unbond optical elements bonded with Norland Optical Adhesives.

