

Ocean Optics HR6 UV-VIS High Resolution Spectrometer

See More by [Ocean Optics](#)



Stock #90-030 **NEW** 1 In Stock

⊖ 1 ⊕ C\$10,959²⁸

ADD TO CART

Volume Pricing

Qty 1+	C\$10,959.20 each
Need More?	Request Quote

Product Downloads

General

OceanDirect & OceanView

Software:

7.2 ms – 5 s

Integration Time:

HR-6UW300-25

Model Number:

Note:

Includes manual QR code, software QR code, calibration reports for wavelength and linearity, 1 m USB cable

Input Port Termination:

SMA905

Grating:

Ruled Diffraction Grating: 600 Grooves/mm, Blazed @ 300nm

Optical Bench:

Cross Czerny Turner

Physical & Mechanical Properties

Slit Width (µm):

25

Weight (kg):

0.9306

Dimensions (mm):

149.0 x 106.4 x 48.2

Optical Properties

Spectral Resolution (nm):

0.57

Wavelength Range (nm):

200 - 650

Sensor

Type of Sensor:

CCD

Electrical

Signal to Noise S/N Ratio:

Single Scan @ 10 ms: 400:1

Max per second with High Speed Averaging Mode: 3500:1

Hardware & Interface Connectivity

Computer Interface:

USB, RS-232

Threading & Mounting

Mounting Threads:

(3) 2-56

Environmental & Durability Factors

Operating Temperature (°C):

0 to +55

Storage Temperature (°C):

-30 to +70

Thermal Stability:

0.02 nm/°C

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 250:

[Compliant](#)

Product Details

- High Resolution Spectrometers for Narrow Peak Identification
- Spectral Ranges Spanning UV-VIS, VIS-NIR, and NIR Wavelengths
- Rapid Acquisition Speed and Excellent Thermal Stability

Ocean Optics HR High Resolution Spectrometers, available in HR2, HR4, and HR6 models, are designed to identify narrow spectral peaks with detailed spectral analysis for applications that require high-resolution solutions. The HR2 spectrometers feature high-resolution performance, fast scan speeds, and excellent thermal stability, providing rapid, real-time results ideal for applications such as plasma monitoring and pharmaceutical analysis. The HR4 spectrometers combine high-resolution spectral analysis with excellent thermal stability, making these models excel in precision-demanding environments such as DNA/RNA analysis, biomedical research, and high-throughput reflection testing. The HR6 spectrometers offer high sensitivity, high resolution, and excellent signal-to-noise ratio (SNR) performance for applications including protein absorbance and emission of broadband sources. The Ocean Optics HR High Resolution Spectrometers include the user-friendly OceanView software system to optimize spectrometer performance, ease system integration, and access data for analysis.