

SCHOTT OG590, 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-418** ☐ In Stock

1

C\$44.80

ADD TO CART

Qty 1-10
C\$44.80
Qty 11+
C\$39.20
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
590.00 ±6

Density (g/cm³):

2.56
Glass/Filter Number: SCHOTT OG590
Coating: Uncoated
Color: Red
Passband Limit 1 λ_{p1} (nm): 660
Index of Refraction n_d: 1.51
Spectral Transmittance t_p (%): 93
Stopband Limit λ_s(nm): 510
Surface Quality: 60-40
Transformation Temperature (°C): 506
Thickness (mm): 1.00 ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--