

[See all 6 Products in Family](#)

Olympus 10X WLI Objective

See More by [Olympus](#)



Stock #91-172 NEW [CONTACT US](#)

-

1

+

C\$6,384^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$6,384.00 each
Need More?	Request Quote

Product Downloads

General	
WL10XMRTC	Model Number:
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm	
Microscope Objective	Type:
Infinity Corrected	Style:
Olympus	Manufacturer:

Note:
Designed to be used with a 180mm Tube Lens, Sold Separately

Physical & Mechanical Properties	
2.2	Field of View (mm):
36.80	Length excluding Threads (mm):
29.7	Maximum Diameter (mm):
Optical Properties	
18.00	Focal Length FL (mm):
10X	Magnification:
0.30	Numerical Aperture NA:
1.12	Resolving Power (µm):
3.06	Depth of Field (µm):
8.2	Working Distance (mm):
22	Field Number (mm):
45	Parfocal Length (mm):
305.6	Depth of Focus (µm):
Threading & Mounting	
RMS / 20.32mm x 36 TPI	Mounting Threads:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:

Product Details

- Combines High Numerical Aperture and Broad Field of View
- Thermal Compensation & Stability Features
- Suitable for 3D Surface Metrology and Profilometry

Olympus WLI Infinity Corrected Interferometry Objectives' advanced optical design combines a high numerical aperture with a broad field of view, capturing fine surface details across large areas for visual clarity. Each objective features a built-in adjustment ring that compensates for temperature-induced focused shifts, allowing stability and consistent measurement accuracy even under unstable environmental conditions. These objectives are designed to be used with a 180mm focal length tube lens and are available in magnification of 10 – 50X. Olympus WLI Infinity Corrected Interferometry Objectives are ideal for 3D surface metrology and profilometry applications, including semiconductor inspection, precision machining, optical coating evaluation, and microelectronic characterization.