

[See all 1 Products in Family](#)

# Sill Optics 163mm FL, 102 x 102mm Scan Area, 532 + 1064nm F-Theta Scanning Lens, S4LFT1163-081

See More by [Sill Optics](#)



Stock #70-153 **3 In Stock**

C\$6,594<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	C\$6,594.00 each
Qty 5+	C\$5,936.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

S4LFT1163-081 **Model Number:**

F-Theta Lens **Type:**

**Physical & Mechanical Properties**

**Maximum Diameter (mm):**

106.00

Flange Distance (mm):

214.5 (@1064) 215.4 (@532)

Input Beam Diameter, 1/e<sup>2</sup> (mm):

12.00

Maximum Length (mm):

82.50

Weight (kg):

1.30

## Optical Properties

Focal Length FL (mm):

163.00

Scan Angle (°):

±25.30

Scan Field (mm):

102.0 x 102.0

Telecentricity (°):

12.7

Transmission (%):

>96

Working Distance (mm):

159.90

Design Wavelength DWL (nm):

532

Wavelength Range (nm):

532, 1064

Coating Specification:

532nm R < 0.25% + 1064nm R < 0.20%

Focus Size Diameter, 1/e<sup>2</sup> (µm):

20.08 (@1064) 13.25 (@532)

Damage Threshold, Pulsed:

2.5 J/cm<sup>2</sup> per 1ns pulse at 50Hz

Damage Threshold, CW:

2.5 MW/cm<sup>2</sup>

## Threading & Mounting

Mounting Threads:

M85 x 1.0

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Multispectral Design Wavelength of 532nm and 1064nm
- Large Scan Field of 102mm x 102mm and a Focal Length of 163mm
- High Damage Thresholds and Low Telecentricity Errors
- [Galvanometers](#), [Beam Expanders](#), and [Laser Sources](#) Also Available

Sill Optics Multispectral F-Theta Lenses are high quality lenses that are ideal agricultural inspection, confocal microscopy, and environmental research applications. This F-Theta Lens offers a focal length of 163mm, and a large scan field of 102mm (X) x 102mm (Y). Corrected for Nd:YAG fundamental wavelength of 1064nm and the second harmonic wavelength for 532nm, this lens features a common mounting thread for easy integration into galvo systems. Sill Optics Multispectral F-Theta Lenses feature a high damage threshold of 2.5 J/cm<sup>2</sup> (1ns, 50Hz) for pulsed lasers and 2.5 MW/cm<sup>2</sup> for continuous wave (CW) lasers.