

[See all 14 Products in Family](#)

Sill Optics 650mm FL, 410 x 410mm Scan Area, 1030-1090nm F-Theta Scanning Lens, S4LFT1655-328

See More by [Sill Optics](#)



Stock #70-145 **3 In Stock**

C\$11,144.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$11,144.00 each
Qty 5+	C\$10,024.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:
 S4LFT1655-328

Type:
 F-Theta Lens

Physical & Mechanical Properties

Maximum Diameter (mm):
 134.00

676.1	Flange Distance (mm):
20.00	Input Beam Diameter, 1/e² (mm):
105.50	Maximum Length (mm):
1.60	Weight (kg):

Optical Properties

650.00	Focal Length FL (mm):
±24.40	Scan Angle (°):
410.0 x 410.0	Scan Field (mm):
22.5	Telecentricity (°):
>98	Transmission (%):
581.60	Working Distance (mm):
1064	Design Wavelength DWL (nm):
1030 - 1090	Wavelength Range (nm):
Coating Specification: 1030nm - 1090nm R < 0.20% - low absorption	
63.29	Focus Size Diameter, 1/e² (μm):
Damage Threshold, Pulsed: 5.0 J/cm ² per 1ns pulse at 50Hz	
Damage Threshold, CW: 5.0 MW/cm ²	

Threading & Mounting

M85 x 1.0	Mounting Threads:
-----------	--------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	------------------------------------

Product Details

- Ideal for High-Precision Material Processing and Laser Scanning Applications
- Large Scan Fields Up to 410mm x 410mm
- High Damage Thresholds and Low Telecentricity Errors
- [Galvanometers](#), [Beam Expanders](#), and [Laser Sources](#) Also Available

Sill Optics F-Theta Lenses are high quality lenses specifically designed for laser material processing applications for industrial mechanical engineering. These F-Theta Lenses offer a wide range of focal lengths up to 650mm, and large scan fields up to 410mm (X) x 410mm (Y). Optimized for Nd:YAG fundamental, second, or third harmonic laser wavelengths, these lenses are available in design wavelengths of 355nm, 532nm, and 1064nm with common mounting threads for easy integration into galvo systems. Sill Optics F-Theta Lenses feature fused silica substrates and utilize a special low-absorption coating to minimize thermal effects and increase damage thresholds up to 5.0 J/cm² (1ns, 50Hz) for pulsed lasers and 5.0 MW/cm² for continuous wave (CW) lasers. These lenses are ideal for a range of material processing and medical applications such as laser cutting, welding, and drilling, confocal microscopy, and ophthalmology.