

Olympus Wide Field Tube Lens, 180mm Focal Length

See More by [Olympus](#)



Olympus Wide Field Tube Lens, #36-401

Stock **#36-401** **2 In Stock**

-

1

+

C\$861^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$861.00 each
Need More?	Request Quote

Product Downloads

General	
SWTLU-C	Model Number:
Olympus	Manufacturer:
Optical Properties	
180.00	Focal Length FL (mm):
1X	Magnification:

400 - 1000	Wavelength Range (nm):
26.5	Field Number (mm):
36.0	Entrance Pupil Diameter (mm):

Threading & Mounting

M41 x0.5	Mounting Threads:
----------	-------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:

Product Details

- High Numerical Aperture (NA) up to 1.45
- Chromatic Aberration Correction from 400 - 1000nm
- Uniform Image Flatness over Large FOVs

Olympus X-Line Extended Apochromat Infinity Corrected Objectives (also referred to as the UPLXAPO series) are Olympus' next generation high performance objectives that simultaneously feature high numerical aperture (NA), broadband chromatic aberration correction, and excellent image flatness. The high numerical aperture (NA) allows for excellent light collection efficiency to better capture faint signals, enabling a shorter exposure time and higher contrast. The broad chromatic aberration correction compensates for the wavelength-dependent spatial shift of colors to achieve excellent color reproduction. These objectives also achieve high image flatness from the center to the edges of images over large fields of view (FOV), making them ideal for image stitching and quantitative image analysis. Olympus X-Line Extended Apochromat Infinity Corrected Objectives are used in demanding life science and clinical applications including pathology, fluorescence microscopy, multicolor or widefield fluorescence imaging, confocal or super resolution microscopy, and whole slide imaging.

Technical Information

	Stock #	A	B	C	D	E	F	G	WD
Olympus UPLXAPO 4X Objective	#14-905	31.89	-	-	15.4	15.4	28	4.7	13.0
Olympus UPLXAPO 10X Objective	#14-906	41.78	3.7	4.28	9.6	19.4	28	4.6	3.1
Olympus UPLXAPO 20X Objective	#14-907	44.28	3.39	2.88	10.2	18.6	28	4.8	0.61
Olympus UPLXAPO 40X Objective	#14-908	44.71	4.21	2.11	7.5	20.3	31.5	4.9	0.18
Olympus UPLXAPO 60X Oil Immersion Objective	#14-909	44.74	2.1	2.84	10	19.3	31.5	4.9	0.15
Olympus UPLXAPO 100X Oil Immersion Objective	#14-910	44.76	2.1	3.06	7.5	19.1	30.5	4.8	0.135

Technical diagram of an Olympus UPLXAPO objective showing dimensions A through G and WD. A is the parfocal length (45.06 mm). B is the distance from the mounting flange to the rear lens. C is the distance from the mounting flange to the front lens. D is the distance from the mounting flange to the objective nose. E is the distance from the mounting flange to the objective body. F is the distance from the mounting flange to the objective tip. G is the distance from the mounting flange to the objective base. WD is the working distance. The diameter of the mounting flange is 20.32 mm.