

[See all 21 Products in Family](#)

# Oryx® ORX-10GS-89S6M-C Mono 10GigE (Recertified 05-P)

See More by [Teledyne FLIR](#)



ORYX-10G-310S9C



Stock **#19-792-RCD-05P** RECERTIFIED **1 In Stock**

[Similar Cameras](#)

-

1

+

C\$6,293<sup>00</sup>

ADD TO CART

| Volume Pricing |                  |
|----------------|------------------|
| Qty 1+         | C\$6,293.00 each |

|                |                               |
|----------------|-------------------------------|
| Volume Pricing |                               |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

|            |           |
|------------|-----------|
| Monochrome | Spectrum: |
|------------|-----------|

General

|                   |                |
|-------------------|----------------|
| Monochrome Camera | Type:          |
| ORX-10GS-89S6M-C  | Model Number:  |
| FLIR              | Manufacturer:  |
| Oryx®             | Camera Series: |

Physical & Mechanical Properties

|              |                  |
|--------------|------------------|
| 60 x 60 x 64 | Dimensions (mm): |
| 386          | Weight (g):      |
| Full         | Housing:         |

Sensor

|                       |                           |
|-----------------------|---------------------------|
| 240MB                 | Image Buffer:             |
| 1"                    | Sensor Format:            |
| 8.90                  | Resolution (Megapixels):  |
| 93.00                 | Frame Rate (fps):         |
| 4,096 x 2,160         | Pixels (H x V):           |
| 3.45 x 3.45           | Pixel Size, H x V (µm):   |
| 14.13 x 7.45          | Sensing Area, H x V (mm): |
| Sony IMX255           | Imaging Sensor:           |
| Progressive Scan CMOS | Type of Sensor:           |
| Global                | Shutter Type:             |
| 8/10/12 Bit           | Pixel Depth:              |
| 5µs - 30s             | Exposure Time:            |
| 71.57                 | Dynamic Range (dB):       |
| GigE Vision           | Machine Vision Standard:  |

Electrical

|      |                        |
|------|------------------------|
| 12.6 | Power Consumption (W): |
|------|------------------------|

Hardware & Interface Connectivity

|                                                                                                                                                                                                           |               |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| 10GigE                                                                                                                                                                                                    | Interface:    |
| GigE interface with Screw Locks                                                                                                                                                                           | Connector:    |
| Power Supply Required and Sold Separately:<br>USA: <a href="#">#19-803</a><br>Europe: <a href="#">#19-803</a><br>Japan: <a href="#">#19-803</a><br>Korea: Not Available<br>China: <a href="#">#19-803</a> | Power Supply: |
| 2 opto-isolated inputs, 2 opto-isolated outputs, 2 non-isolated bi-directional                                                                                                                            | GPIOs:        |

|                                                                                      |  |
|--------------------------------------------------------------------------------------|--|
| <b>Synchronization:</b><br>Hardware Trigger (GPIO) or Software Trigger               |  |
| <b>Interface Port Orientation:</b><br>Back Panel                                     |  |
| <b>GPIO Connector Type:</b><br>12-pin Hirose (HR10)                                  |  |
| <b>Threading &amp; Mounting</b>                                                      |  |
| <b>Mount:</b><br>C-Mount                                                             |  |
| <b>Mounting Threads:</b><br>1/4-20 with Tripod Mount Adapter <a href="#">#19-804</a> |  |
| <b>Environmental &amp; Durability Factors</b>                                        |  |
| <b>Operating Temperature (°C):</b><br>0 to +70                                       |  |
| <b>Storage Temperature (°C):</b><br>-30 to +60                                       |  |
| <b>Regulatory Compliance</b>                                                         |  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a>                           |  |

## Product Details

- 10GBASE-T (10GigE) Ethernet Interface
- 3.2 to 31 Megapixel Sony 4th Gen Pregius S Sensors
- Supports 4K60, 12-bit System Integration
- Tripod Adapter Built into Larger Oryx® Models



### Teledyne FLIR IIS Oryx 10GgE: High throughput, Award-winning camera designs

Reliably capture images at high speed

The **Oryx 10GgE** camera family supports transfer speeds of up to 10 Gbit/s enabling capture of 4K resolution, 12-bit images at speeds exceeding 60 FPS. Reliable image transfer at high bandwidth is further improved with Myricom bundles and packet resend feature. A range of sensor options offer resolutions from 3.2 Megapixel up to 31 Megapixel. Oryx features include IEEE1588 clock synchronization and full compatibility with several popular third-party software supporting GigE Vision. Oryx's 10GBASE-T interface is a proven and widely deployed standard that provides reliable image transfer at cable lengths over 50 meters on inexpensive CAT6A, and up to 30 meters on CAT5e.

**Note:** The ORX-10G-310S9 and ORX-10G-245S8 cameras require an F-Mount lens adapter (sold separately).

#### Features

- Color or monochrome sensors
- Various frame triggering options including up to 8 sets of 2-feature sequencer
- Pixel binning, decimation, ROI
- On camera image processing includes Gamma, LUT, and sharpness

#### Applications

- Stadium venues
- Site security
- Factory automation
- Traffic monitoring
- Inspection systems

## Calibration Services